




N°		CODE Кодировка
1		HD006000
2		HD018000
3		HD021000
4	(4 Unit)	HD026055
5	(4 Unit)	HD031010
6	(4 Unit)	HD031055
7		HD036000
8		HD021100
9		HD041000
10		HD021035
11		HD046005
12		HD031075
13	0,33 CV	HD051005
13	0,50 CV	HD051010
13	0,75 CV	HD051015
13	1 CV	HD051025
13	1,5 CV	HD051035
14		HD021060
15		HD056005

N°		CODE Кодировка
16	0,33 / 0,50 CV	HD061000
16	0,75 / 1 / 1,5 CV	HD061005
17		HD066000
18	0,33 / 0,50 CV	HD071005
18	0,75 / 1 / 1,5 CV	HD071000
19	(2 Unit)	MT001000
20	0,33 / 0,50 CV	MT006025
20	0,75 / 1 / 1,5 CV	MT006050
21	(2 Unit)	MT026000
24		MT081030
26	1-PH	MT081035
26	3-PH	MT081045
27		MT076050
28	1-PH	MT088000
28	3-PH	MT088005
29	0,33 / 0,50 CV 1-PH	MT091000
29	0,75 / 1 / 1,5 CV 1-PH	MT091010
30		MT096000
31	0,33 / 0,50 CV	MT016025
31	0,75 / 1 / 1,5 CV	MT016040

N°		CODE Кодировка
32	0,33 / 0,50 CV (4 Unit)	MT101015
32	0,75 / 1 / 1,5 CV (4 Unit)	MT101040
33	0,33 / 0,50 CV	MT086040
33	0,75 / 1 / 1,5 CV	MT086045
34	0,33 / 0,50 CV	MT086050
34	0,75 / 1 / 1,5 CV	MT086051
35	0,33 / 0,50 CV	MT086055
35	0,75 / 1 / 1,5 CV	MT086060
36	(2 Unit)	HD076010
37	(2 Unit)	HD021115
38	(2 Unit)	HD076005
39		HD076000
40	0,33 CV 1-PH	MT999000
40	0,50 CV 1-PH	MT999005
40	0,75 CV 1-PH	MT999010
40	0,75 CV 3-PH	MT999015
40	1 CV 1-PH	MT999020
40	1 CV 3-PH	MT999025
40	1,5 CV 1-PH	MT999030
40	1,5 CV 3-PH	MT999035